


TECHSPEC® 1060nm, 12.7mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock #26-838 20+ In Stock

-

1

+

€105<sup>,00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €105,00 each                  |
| Qty 6-25       | €93,50 each                   |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

6.35 ±0.20

Thickness (mm):

12.70 +0.00/-0.10

Diameter (mm):

|                                                                                                                                      |                             |
|--------------------------------------------------------------------------------------------------------------------------------------|-----------------------------|
| 90                                                                                                                                   | Clear Aperture (%):         |
| Commercial Polish                                                                                                                    | Back Surface:               |
| <3                                                                                                                                   | Parallelism (arcmin):       |
| Optical Properties                                                                                                                   |                             |
| Fused Silica (Corning 7980)                                                                                                          | Substrate: □                |
| 10-5                                                                                                                                 | Surface Quality:            |
| 45                                                                                                                                   | Angle of Incidence (°):     |
| Ultrafast (1010-1110nm)                                                                                                              | Coating:                    |
| 1060                                                                                                                                 | Design Wavelength DWL (nm): |
| 1010 - 1110                                                                                                                          | Wavelength Range (nm):      |
| λ/8                                                                                                                                  | Surface Flatness (P-V):     |
| Coating Specification:<br>R <sub>(avg)</sub> S & P >99.90% @ 1060nm @ 45° AOI<br>R <sub>(avg)</sub> >99.7% @ 1010 - 1110nm @ 45° AOI |                             |
| Dielectric                                                                                                                           | Coating Type:               |
| GDD Specification:<br>±10 fs <sup>2</sup> @ 1010 – 1110nm @ 45° AOI (s-pol)<br>±30 fs <sup>2</sup> @ 1030 – 1090nm @ 45° AOI (p-pol) |                             |
| Environmental & Durability Factors                                                                                                   |                             |
| MIL-PRF-13830B                                                                                                                       | Durability:                 |
| Regulatory Compliance                                                                                                                |                             |
| View                                                                                                                                 | Certificate of Conformance: |

## Product Details

- GDD as Low as ±20fs<sup>2</sup> at Design Wavelength Range
- Greater than 99.9% Reflectivity
- Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers

TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.

**Note:** Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).