

LightPath 354240 | 1064nm Alignment, 0.50 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#64-782** 3-4 DAYS



1



€205,00

ADD TO CART

Qty 1-10

€205,00

Qty 11+

€181,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
8.00 @ 780nm

Numerical Aperture NA:
0.50

Substrate: ECO-550
Coating: BBAR (1050-1600nm)
Coating Specification: Rabs <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 8.00
f#: 1.00
Bevel: Protective bevel as needed
Connector: SMA
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 12.00
Housing Length (mm): 12.7
Lightpath Lens Code: 354240
Mount: M12 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 1050 - 1600
Conjugate Distance: Infinite
Lens Included: #37-104
Alignment Wavelength (nm): 1064

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant