


[See all 32 Products in Family](#)

# 1064nm, 15-20mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper\_1064\_Q-17

See More by [AdiOptica](#)



Focal Flat Top Beam Shaper



Stock #12-236 [CONTACT US](#)

⊖ 1 ⊕ €2.830<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€2.830,00 each
Qty 5-10	€2.545,00 each
Qty 11+	€2.410,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

## General

Model Number:  
πShaper\_1064\_Q-17

Beam Shaper **Type:**

[#12-323](#) **Compatible Adapter:**

## Physical & Mechanical Properties

21.00 **Length (mm):**

70 **Weight (g):**

38 **Clear Aperture CA (mm):**

64.00 **Diameter (mm):**

15 - 20 **Input Beam Diameter,  $1/e^2$  (mm):**

## Optical Properties

>99 **Transmission (%):**

1064 **Design Wavelength DWL (nm):**

1020 - 1100 **Wavelength Range (nm):**

TEM<sub>00</sub> **Input Beam Mode:**

<1.5 **Typical Input Beam Mode Quality,  $M^2$ :**

±20 **Input Beam Divergence (mrad):**

## Electrical

0.4 **Maximum Input Power, CW (kW):**

## Threading & Mounting

M58 x 1 **Inner Thread:**

M58 x 1 **Outer Thread:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

## Product Details

- Shapes Gaussian Beams to Airy Disk Profile
- Airy Disk is Focusable to Flat Top Spot
- Near 100% Efficiency
- [AdlOptica  \$\pi\$ Shaper Flat Top Beam Shapers](#) Also Available

AdlOptica Focal- $\pi$ Shaper (piShaper) Q Flat Top Beam Shapers are used to transform Gaussian beams to flat-top profiles after focusing through a lens. This is accomplished by transforming the Gaussian beam to airy disk profiles immediately after the piShaper. These beam shapers feature a compact design with inner and outer threading, making them easy to integrate into equipment. AdlOptica Focal- $\pi$ Shapers are advantageous for beam shaping in micromachining applications, including scribing and PCB drilling, as well as micro-welding applications. Multiple models are available at Nd:YAG, Ti:Sapphire, and Infrared wavelengths with compatible input beam diameters as small as 2.5mm and up to 23mm.

## Technical Information

