


[See all 12 Products in Family](#)

## 10µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-734 NEW 3 In Stock

-
1
+
€185<sup>.00</sup>

ADD TO CART

| Volume Pricing |  |
|----------------|--|
| Qty 1+         | €185,00 each   |
| Need More?     | <a href="#" style="color: #007bff; text-decoration: none;">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

### Physical & Mechanical Properties

Outer Diameter (mm):  
25.4

Fixed Aperture Diameter (µm):  
10 ±1.0

Thickness (inches):  
0.06 ±0.004

Thickness (mm):  
1.52

Thickness Tolerance (mm):

±0.1

## Optical Properties

Low Reflective Chrome

Coating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10µm to 1,000µm

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10µm to 1000µm. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.