


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 10mm 266nm, Laser Line $\lambda/20$ High Tolerance Right Angle Mirror



Stock #37-641 3-4 DAYS

⊖ 1 ⊕ **€232,00**

ADD TO CART

Qty 1-5

€232,00

Qty 6+

€185,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/20$

Substrate:
[Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Length of Legs (mm):
10.00

Dimensional Tolerance (mm):
+0.00/-0.10

Coating Specification:
R_{abs} >99.5% @ 266nm @ 45° AOI
R_{avg} >99.5% @ 263 - 268nm @ 45° AOI

Coating:
Laser Mirror (266nm)

Bevel:
Protective bevel as needed

Clear Aperture (%):
90

Design Wavelength DWL (nm):
266

Length of Hypotenuse (mm):
14.10

Type:
Right Angle Mirror

Pyramid Tolerance (arcmin):
±1

Angle Tolerance (arcsec):
±15

Damage Threshold, Reference: □
1MW/cm² @ 266nm

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 209:
[Compliant](#)

Certificate of Conformance:
[View](#)
