

[See all 13 Products in Family](#)

10mm Aperture, Protected Silver, Compact 506 Dual Axis Galvanometer Scanner

See More by [ScannerMAX](#)



10mm Aperture, Protected Silver, Compact 506 Dual Axis Galvanometer Scanner



Stock **#16-038** **1 In Stock**

⊖ 1 ⊕ €2.940⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.940,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Dual Axis **Type:**
ScannerMAX Compact 506 **Model Number:**

Physical & Mechanical Properties

10	Mirror Aperture (mm):
44.0 x 33.0 x 47.8 (of mount. Galvos protrude ~17mm)	Dimensions (mm):
0.014	Rotor Inertia (gm-cm²):
18,400	Torque Constant (dyne-cm/A):
400	Step Response 0.1° (μs):

Optical Properties

≤λ/4 @ 632.8nm	Surface Flatness (P-V):
Protected Silver	Coating:
40 (Optical)	Scan Angle (°):
Silicon (Si)	Substrate: □

Electrical

±10	Position Signal (V):
Maximum: 10	Current - Peak (A):
1.85 (Case @ 50°C)	Current - RMS (A):
1.8	Coil Resistance (Ω):
280	Coil Inductance (μH):
32.1	Back EMF Voltage (μV/°/s):

Hardware & Interface Connectivity

±24 VDC	Power Requirement:
1 x #16-045 Europe (CE Marked): 2 x #14-571	Power Supply:

Environmental & Durability Factors

0 to +50	Operating Temperature (°C):
----------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- 3, 5, and 10mm Mirror Apertures
- Dual Axis Configuration with Protected Silver Coating
- Compact, Light-Weight, Low-Cost Scanners
- [High Performance ScannerMAX Saturn Scanners](#) Also Available

ScannerMAX Compact 506 Dual Axis Galvanometer Optical Scanners are designed for cost-sensitive applications requiring compact, light-weight optical scanners that do not compromise on performance. The Compact 506 series features a sturdy rotor construction and low coil resistance, allowing these galvanometers to achieve reasonably fast scan speeds without producing excessive heat. The patented position sensor design provides these galvanometers with up to ten times the signal-to-noise ratio of conventional galvanometers, ensuring high quality motion. ScannerMAX Compact 506 Dual Axis Galvanometer Optical Scanners are ideal for use in stereo lithography (SLA) 3D printing, LiDAR, handheld medical devices, and laser cleaning applications. Optical scanners with a 3, 5, and 10mm mirror aperture are available with a protected silver coating; please contact us if your application requires a Compact 506 galvanometer scanner with a custom mirror aperture or coating.

ScannerMAX Compact 506 Galvanometer Optical Scanners are driven by the Mach-DSP Servo Driver. This digital servo driver features a compact package size and simultaneously control both X-Axis and Y-Axis scanners. The Mach-DSP can be controlled by both analog and digital signals, and it can be accessed and adjusted using a free GUI software package, which includes a built-in test pattern generator, oscilloscope, and dynamic signal analyzer. The Mach-DSP Servo Driver requires ±24 VDC of power.

Note: For European customers, 2 units of power supply #14-571 are required for operation.

Various longer or shorter galvo to servo cables are available in the accessories tab. Please note that these cables are compatible with all Compact 506 Systems as well as the following list of Saturn Systems:

Any Saturn 1 System (16-039 or 16-042) with Serial Numbers higher than PS102838
Any Saturn 5 System (16-040 or 16-043) with Serial Numbers higher than PS501904
Any Saturn 9 System (16-041, 16-044, 21-969) with Serial Numbers higher than PS903670

Each Compact 506 Dual Axis Galvanometer Optical Scanner ships with:

- 2 x Compact 506 Series Galvanometer
- 1 x X-Y Axis Mount
- 1 x Mach-DSP Servo Driver Board

- 2 x 1-meter-long cables that connect the galvanometer to the servo driver
- 1 x Cable kit including power and analog input cables

Technical Information

WHAT'S INCLUDED WITH YOUR SCANNERMAX SCANNER	
Item Number	Description
1	Galvo to Servo Driver Connection Cable (1 with Single Axis Scanners, 2 with Dual Axis)
2	Digital Input Cable for Servo Driver
3	Analog Input Cable for Servo Driver
4	Mach-DSP Servo Driver Board
5	Galvanometer
6	Thermal Paste
7	Power Cable