

TECHSPEC® 10mm Diameter Enhanced Aluminum Coated, λ/10 Mirror



Stock **#64-009** 3-4 DAYS

⊖ 1 ⊕ **€77,50**

ADD TO CART

Qty 1-5
€77,50

Qty 6+
€62,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm): 10.00 +0.00/-0.20
Surface Flatness (P-V): λ/10 (measured before coating)
Substrate: ☐ Fused Silica (Corning 7980)

Back Surface: Commercial Polish
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 2.00 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant