


## TECHSPEC® 10mm Diameter x 1.75mm Thickness, NIR Coated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock #12-185 **20+ In Stock**

⊖ 1 ⊕ €38<sup>75</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€38,75 each
Qty 6-25	€31,00 each
Qty 26-99	€28,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

## SPECIFICATIONS

### General

Protective Window

Type:

## Physical & Mechanical Properties

Protective as needed	<b>Bevel:</b>
≥90	<b>Clear Aperture (%):</b>
9.00	<b>Clear Aperture CA (mm):</b>
10.00 ±0.5	<b>Diameter (mm):</b>
1.75 ±0.2	<b>Thickness (mm):</b>
Ground	<b>Edges:</b>
480.00	<b>Knoop Hardness (kg/mm<sup>2</sup>):</b>
0.20	<b>Poisson's Ratio:</b>
64	<b>Young's Modulus (GPa):</b>

## Optical Properties

65.41	<b>Abbe Number (v<sub>d</sub>):</b>
NIR (700-1150nm)	<b>Coating:</b>
R <sub>avg</sub> <1.0% @ 700 - 1150nm	<b>Coating Specification:</b>
1.472	<b>Index of Refraction (n<sub>d</sub>):</b>
<b>BOROFLOAT®</b>	<b>Substrate:</b>
4 - 6λ	<b>Surface Flatness (P-V):</b>
80-50	<b>Surface Quality:</b>
≥97	<b>Transmission (%):</b>
700 - 1150	<b>Wavelength Range (nm):</b>

## Material Properties

3.25 (+20 to +300°C)	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
2.23	<b>Density (g/cm<sup>3</sup>):</b>
525	<b>Transformation Temperature (°C):</b>

## Environmental & Durability Factors

1 hour @ 500; >100 hours @ 450	<b>Operating Temperature (°C):</b>
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	<b>Resistance to Temperature Difference (K):</b>
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	<b>Thermal Shock (K):</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## PRODUCT DETAILS


- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C).  
TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness — typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

## TECHNICAL INFORMATION

### BOROFLOAT®



## QUOTE YOUR SIZE

## COMPATIBLE MOUNTS