

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 10mm Sq., 2mm Thick, NIR I Coated M4 N-BK7 window



Stock #83-467 3-4 DAYS



1



€76,50

ADD TO CART

Qty 1-5

€76,50

Qty 6+

€61,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number ( $v_d$ ):  
64.17

Bevel:  
Protective as needed

Clear Aperture (%):  
90

|                                                                                                                      |
|----------------------------------------------------------------------------------------------------------------------|
| <div>Clear Aperture CA (mm):<br/>9.00 x 9.00</div>                                                                   |
| <div>Dimensions (mm):<br/>10.00 x 10.00</div>                                                                        |
| <div>Thickness (mm):<br/>2.00 ±0.20</div>                                                                            |
| <div>Coating:<br/>NIR I (600-1050nm)</div>                                                                           |
| <div>Coating Specification:<br/>R<sub>avg</sub> ≤0.5% @ 600 - 1050nm</div>                                           |
| <div>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):<br/>7.1 (-30 to +70°C)<br/>8.3 (+20 to +300°C)</div> |
| <div>Density (g/cm³):<br/>2.51</div>                                                                                 |
| <div>Edges:<br/>Fine Ground</div>                                                                                    |
| <div>Index of Refraction n<sub>d</sub>:<br/>1.516</div>                                                              |
| <div>Knoop Hardness (kg/mm²):<br/>610</div>                                                                          |
| <div>Parallelism (arcmin):<br/>&lt;1</div>                                                                           |
| <div>Poisson's Ratio:<br/>0.206</div>                                                                                |
| <div>Substrate:<br/><a href="#">N-BK7</a></div>                                                                      |
| <div>Surface Flatness (P-V):<br/>λ/4</div>                                                                           |
| <div>Surface Quality:<br/>60-40</div>                                                                                |
| <div>Type:<br/>Protective Window</div>                                                                               |
| <div>Wavelength Range (nm):<br/>600 - 1050</div>                                                                     |
| <div>Young's Modulus (GPa):<br/>82</div>                                                                             |
| <div>Length (mm):<br/>10.00</div>                                                                                    |
| <div>Width (mm):<br/>10.00</div>                                                                                     |
| <div>Damage Threshold, By Design: <input type="checkbox"/><br/>7 J/cm² @ 1064nm, 10ns</div>                          |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
| <div>Reach 235:<br/><a href="#">Compliant</a></div>             |