

[See all 24 Products in Family](#)

10mW, 473nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock **#19-469** **1 In Stock**

⊖ 1 ⊕ €1.195⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€1.195,00 each
Qty 10+	€1.076,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads



General

Note:
Compatible TEC Controller ([#19-476](#)) sold separately

Laser Class - CDRH:
IIIb

Physical & Mechanical Properties

Length (mm):
100.00

Optical Properties

TEM₀₀ **Spatial Mode:**

473.00 ±1 **Wavelength (nm):**

1.5 Typical **Beam Diameter (mm):**

<1.5 Typical **Beam Divergence (mrad):**

Blue **Color:**

Electrical

10 **Output Power (mW):**

Not Modulated **Modulation Frequency (kHz):**

Hardware & Interface Connectivity

3 **Operating Voltage (V):**

Power Supply:
Power Supply Required and Sold Separately:
USA: [#19-475](#)
Europe: [#19-475](#)
Japan: Not Available
Korea: Not Available
China: [#19-475](#)

Environmental & Durability Factors

23 to 27 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 233:**

Product Details

- TTL Modulation up to 10kHz
- Transverse Mode TEM₀₀
- Blue, Green, Yellow, and IR Output Wavelengths
- TEC or Heatsink Required for Operation ([Sold Separately](#))

DPSS Pointing Lasers are diode pumped solid state lasers available in output powers ranging from 1 to 100mW. With their solid state design, these lasers offer excellent mode purity and low divergence, making them ideal for applications that require long projection distances. The turnkey design featuring integrated optics and electronics in a single package is suitable for a variety of plug and play operations. DPSS Pointing Lasers provide high brightness circular output beams and are ideal for many different OEM applications. TEC Controller or heatsink is required to maintain 23°C – 27°C operating temperature range.

Note: Power supplies, TEC Controller ([#19-476](#)), Line Projection Heads (for 532nm - [#37-093](#))(for 1064nm - [#37-097](#)), and mounting brackets ([#37-144](#)) are sold separately.