

10X (13 - 130mm FL) C-Mount, Close Focus Zoom Lens



10X (13 - 130mm FL) C-Mount, Close Focus Zoom Lens, #54-363

Stock **#54-363** 1 In Stock

-

1

+

€770⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€770,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Minimum: 0.82X - 0.085X Maximum: 0.23X - 0.023X	Note:
Macro Zoom Lens	Type:

Physical & Mechanical Properties

98.50	Length (mm):
-------	--------------

48.00	Maximum Diameter (mm):
233.00	Weight (g):
Optical Properties	
7.8 - 280mm	Horizontal Field of View, 1/2" Sensor:
10:1	Zoom Ratio:
13-130	Focal Length Range (mm):
0.82X - 0.023X	Primary Magnification PMAG:
152 - 457	Working Distance (mm):
f/5.6 - f/32	Aperture (f/#):
VS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
Threading & Mounting	
M46 x0.75	Filter Thread:
C-Mbunt	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Large Zoom
- Close Focus Capability
- Broad Field of View Range

Close Focus Zoom Lenses are ideal for multipurpose applications that need both close focus and wide fields of view. The lenses offer variable apertures, to adjust the depth of field. Filter threading allows the use of filters to adjust incoming light levels with ND filters, or increase contrast with color filters on monochrome sensors, and more. Close Focus Zoom Lenses are economical and compact, and these lenses have many features that make them a perfect choice for a variety of uses. These zoom lenses feature 10X magnification and are compatible with C-mounts.

Note: #58-240 Close Focus Zoom Lens can be used for working distances from 127mm to infinity, where its field of view would be 8 - 48mm (horizontal for 2/3" sensors) at minimum working distance.

Technical Information

