

10X Focusing Lens



10X Focusing Lens



Stock **#28-779** 1 In Stock

-

1

+

€395^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€395,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Use with #15-943 instead of #18-509 for uniform in-line illumination.

Physical & Mechanical Properties

104.23Length (mm):

Maximum Diameter (mm):

Threading & Mounting

Mounting Threads:

Regulatory Compliance

Certificate of Conformance:

Product Details


- Up to 43% Smaller than Industry Standard Systems
- Optimized Performance up to 1.1" Sensor
- Ideal for Life Science and Industrial Applications
- Winner of the **2023 Bronze VSD Innovators Award**

Edmund Optics® 120i Plan APO Infinity Corrected Objectives are infinite conjugate microscope objectives that offer exception image flatness and chromatic correction over 400-700nm. These objectives were designed for a 1.1" sensor to offer a large field of view and reliable image quality for high-throughput imaging applications. Ideal for life science and machine vision applications such as microscopy, flow cytometry, pharmaceutical inspection, and assembly line or fault inspection.

These objectives won the **2023 Bronze VSD Innovators Award**.

Technical Information

Compact Tube Lens System



Standard Tube Lens System

