

[See all 6 Products in Family](#)

## 10X Water Immersion Objective, Nikon CFI60 Plan Fluor

See More by [Nikon](#)



Stock #90-615 **NEW** 1 In Stock

⊖ 1 ⊕ €2.905<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€2.905,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

MRH07120 **Model Number:**

**Compatible Tube Lens Focal Length (mm):**  
Focal Length: 200mm

Microscope Objective **Type:**

Infinity Corrected **Style:**

Nikon

Manufacturer:

## Physical & Mechanical Properties

2.5 Field of View (mm):

56.90 Length excluding Threads (mm):

28 Maximum Diameter (mm):

110 Weight (g):

## Optical Properties

N/A Compatible Cover Glass Thickness (mm):

0.64 Horizontal Field of View, 1/2" Sensor:

0.88 Horizontal Field of View, 2/3" Sensor:

10X Magnification:

0.30 Numerical Aperture NA:

3.5 Working Distance (mm):

25 Field Number (mm):

60.5 Parfocal Length (mm):

Water Immersion Liquid:

## Sensor

2/3" Maximum Sensor Format:

## Threading & Mounting

M25 x 0.75 Mounting Threads:

## Regulatory Compliance

[View](#) Certificate of Conformance:

## Product Details

- Water Dipping Design for Live Imaging
- Optimized for Infrared (IR) and Multiphoton Microscopy
- High NA for Superior Resolution

Nikon CFI60 Water Dipping Objectives design allows direct immersion into aqueous samples, reducing optical aberrations and enabling high-resolution, live imaging of thick specimens. These objectives are designed with high numerical apertures and long working distances and are available in a variety of magnifications. Featuring M25 x 0.75 mounting threads, these objectives can be easily integrated into existing microscopy systems. Nikon CFI60 Water Dipping Objectives enable high-resolution, low-aberration imaging deep within living tissues by efficiently transmitting infrared light and correcting optical distortions specific to multiphoton and IR microscopy.

## Technical Information

