

[See all 10 Products in Family](#)

TECHSPEC® 1:1 with 100mm and 100mm EFL Achromats, NIR Achromatic Pair



TECHSPEC Mounted Near-IR (NIR) Achromatic Lens Pairs

Stock **#47-302** **2 In Stock**

⊖ 1 ⊕ €274⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€274,00 each
Qty 6-25	€219,00 each
Qty 26-49	€212,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Relay Lens **Type:**

Physical & Mechanical Properties

22.0 **Clear Aperture CA (mm):**

Center Air Spacing (mm):

5.45

30.0 +0.0/-0.10 **Housing Diameter (mm):**

34.00 ±0.2 **Housing Length (mm):**

89.50 **Image Distance (mm):**

Construction:
Achromat Pair in Anodized Aluminum Housing

Optical Properties

Substrate: □
N-LAK22 / N-SF6 / N-LAK22 / N-SF6

40-20 **Surface Quality:**

f/4.54 **Working f##:**

NIR II (750-1550nm) **Coating:**

Coating Specification:
R_{abs} ≤1.5% @ 750 - 800nm
R_{abs} ≤1.0% @ 800 - 1550nm
R_{avg} ≤0.7% @ 750 - 1550nm

100.00 **Effective Focal Length EFL A (mm):**

100.00 **Effective Focal Length EFL B (mm):**

1:1 **Magnification:**

89.50 **Object Distance (mm):**

750 - 1550 **Wavelength Range (nm):**

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- 30mm Diameter Package Designed for NIR Applications
- Optimized for Various Magnification Ratios
- Ideal for Integration into OEM Applications
- NIR II Coated for 750-1550nm

Our 15.0mm and 30.0mm Mounted Achromatic Pairs combine our popular TECHSPEC® achromats into common configurations used for relay and projection applications. Packaged in a slim-line aluminum housing, each pair is ready for integration into a host of OEM applications, eliminating the need to handle loose optics. Each lens has also been oriented for optimum system performance. All lenses AR coated. Lower f## pairs may not be ideal for imaging applications depending on the performance requirements. Cylinder lenses can be incorporated into empty barrels in order to generate lines or sheets of light.

Technical Information

