

(12.5-75mm FL), 6X Manual Zoom Video Lens



#53-153

Stock **#53-153** [CONTACT US](#)

-

1

+

€635⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€635,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Macro Zoom Lens

Physical & Mechanical Properties

Length (mm):

114.50

Maximum Diameter (mm):

57.00

Weight (g):

Optical Properties

Field of View @ Min Working Distance (mm):
495 - 86

Horizontal Field of View, 1/2" Sensor:
27.8° - 4.9°

Zoom Ratio:
6:1

Focal Length Range (mm):
12.5-75

Working Distance (mm):
1,000 - ∞

Aperture (f/#):
f/1.2 - f/16

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
2/3"

Threading & Mounting

Filter Thread:
M55.0 x0.75

Mount:
C-Mount

Regulatory Compliance

RoHS 2015:
Exempt

Reach 224:
Contains SVHC(s)

Certificate of Conformance:
View

Product Details

- Manual Zoom, Focus and Iris Control
- Features Locking Set Screws
- C-Mount

Manual Zoom Imaging Lenses provide manual adjustment of focal length (zoom), iris, and focus. Zoom lenses cover the focal length range of several fixed focal length lenses in one lens. Manual Zoom Imaging Lenses should be used when a variable angle field of view is required. Ideal applications include inspection, machine vision, and robotics.

Technical Information

