

TECHSPEC® 12.5mm 850nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-867** **20+ In Stock**

⊖ 1 ⊕ €287⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €287,00 each |
| Qty 6-25 | €232,00 each |
| Qty 26-99 | €211,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

Protective as needed **Bevel:**

Clear Aperture (%):

90.00

Construction:

Cube

Dimensions (mm):

12.5 x 12.5 x 12.5 ±0.1

Optical Properties

Beam Deviation (arcmin):

±3

Coating Specification:

R_{abs} <0.25% @ 850nm

Design Wavelength DWL (nm):

850

Extinction Ratio:

1000:1

P-Polarization Transmission (%):

>95

S-Polarization Reflection (%):

>99.5

Substrate:

N-BK7

Surface Quality:

40-20

Power (fringes) @ 632.8nm:

1.25

Irregularity (fringes) @ 632.8nm:

0.25

Regulatory Compliance

RoHS 2015:

Compliant

Reach 219:

Compliant


Certificate of Conformance:

[View](#)

Product Details

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision [right angle prisms](#) cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.

LASER OPTICS MADE BY EDMUND OPTICS®  [LEARN MORE](#)

Technical Information

