

12.5 x 12.5mm, 30R/70T, AR Coated Plate Beamsplitter



Stock #13-397 **20+ In Stock**

€54^{.50}

ADD TO CART

Volume Pricing	
Qty 1-9	€54,50 each
Qty 10-24	€37,00 each
Qty 25-49	€35,75 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

AR Coated Beamsplitter **Type:**

Physical & Mechanical Properties

>85 **Clear Aperture (%):**

Plate **Construction:**

± 0.38	Dimensional Tolerance (mm):
12.50 x 12.50	Dimensions (mm):
Cut	Edges:
1.00	Thickness (mm):

Optical Properties

Coating Specification:	
Surface 1: Dielectric, $\pm 5\%$ R/T @ 550nm	
Surface 2: AR $N/10$ MgF2 @ 550nm	
30/70	Reflection/Transmission Ratio (R/T):
Float Glass	Substrate: <input type="checkbox"/>
4 - 6 λ	Surface Flatness (P-V):
80-50	Surface Quality:
400 - 700	Wavelength Range (nm):

Regulatory Compliance



Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:



Product Details

- Low-Cost Design
- Multiple Sizes Available
- Many Beamsplitting Ratios Available

Plate Beamsplitters are available in multiple Reflect/Transmission ratios to meet a wide variety of application needs. These beamsplitters are also offered with an anti-reflection (AR) coating on the second surface to enhance each beamsplitter's overall efficiency. This second coating aides in preventing unwanted ghost reflections. Plate Beamsplitters are a cost-efficient option to integrate into multiple applications. For custom sizes or alternate reflection/transmission ratios, please contact our [Sales Department](#).

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).