

TECHSPEC[®] 12.5/12.7mm Optic Dia., Compact Kinematic Mount, 2-Screws



12.5/12.7mm Diameter Compact Kinematic Mount, 2-Screws, #34-720

Stock **#34-720** 20+ In Stock

-

1

+

€101⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€101,00 each
Qty 5-9	€90,90 each
Qty 10+	€83,90 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
Circular	Type of Optics:
2	Number of Adjustment Screws:

22.5 x 22.5	Plate Dimensions (mm):
Physical & Mechanical Properties	
10.9	Clear Aperture CA (mm):
19.60	Thickness (mm):
No Z-Axis Translation	Travel (mm):
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings	
±5	Fine Tilt Angle (°):
±5	Fine Tip Angle (°):
0.2	Adjustment Screw Pitch (mm):
1.9	Min. Thickness of Compatible Optics (mm):
15.0	Centerline Height (mm):
19.6	Thickness of Front Plate to Back Plate (mm):
1.3	Pointing Stability (μrad):
Threading & Mounting	
12.5 - 12.7	Size of Compatible Optics (mm):
M4 x 0.7	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- M3 x 0.2 Fine Adjustment Screw Threads
- <25mm Overall Profile
- Lockable for Improved Stability

Our TECHSPEC® Compact Kinematics are designed to retain the performance of a larger kinematic for integration into space sensitive applications. These kinematics feature completely reseding adjustment screws for integration into OEM applications. TECHSPEC Compact Kinematic Mounts have two front plate models for utilization of set screw or adhesive optic securing. Stainless steel inserts are also used to ensure quality and stability. These kinematic mounts, in conjunction with our [TECHSPEC Laser Mirrors](#), are ideal for reliable integration into laser machining, cinema or life science applications.