


[See all 8 Products in Family](#)

**TECHSPEC® 12.5mm Dia., 1mm Thick, Uncoated, Lithium Fluoride (LiF) Window**



Lithium Fluoride (LiF) Windows

Stock **#19-726** **1 In Stock**

⊖ 1 ⊕ €233.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€233,00 each
Qty 11-25	€210,00 each
Qty 26-49	€198,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Protective Window **Type:**

**Physical & Mechanical Properties**

Protective as needed **Bevel:**

**Clear Aperture (%):**

11.25	Clear Aperture CA (mm):
12.50 +0.00/-0.10	Diameter (mm):
1.00 ±0.10	Thickness (mm):
Fine Ground	Edges:
102.00	Knoop Hardness (kg/mm <sup>2</sup> ):
<3	Parallelism (arcmin):
0.33	Poisson's Ratio:
64.97	Young's Modulus (GPa):

## Optical Properties

97.29	Abbe Number ( $v_d$ ):
Random	Axis Orientation:
Uncoated	Coating:
1.392	Index of Refraction ( $n_d$ ):
Lithium Fluoride (LiF)	Substrate:
$\lambda/2$ @ 632.8nm	Surface Flatness (P-V):
60-40	Surface Quality:
150 - 6000	Wavelength Range (nm):

## Material Properties

37	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):
2.64	Density (g/cm <sup>3</sup> ):

## Regulatory Compliance

<a href="#">View</a>	Certificate of Conformance:
----------------------	-----------------------------


## Product Details

- High Transmission from 150nm - 6 $\mu$ m
- Excellent Vacuum UV (VUV) Transmission
- Low Index of Refraction

Lithium Fluoride (LiF) Windows provide high, flat transmission from 150nm to 6 $\mu$ m. Lithium fluoride has excellent transmission in the vacuum ultraviolet (VUV) wavelength range of 150 - 200nm. Lithium fluoride also has a low index of refraction, allowing these windows to be used without an anti-reflection (AR) coating. Lithium Fluoride (LiF) Windows are ideal for use as UV transmission windows in spectroscopy applications, as a diffracting element in X-ray spectrometry, or as infrared windows for thermal imaging applications.

**Note:** Lithium fluoride is sensitive to thermal shock and is attacked by atmospheric moisture at temperatures above 400°C.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

---