

TECHSPEC® 12.5mm Dia. 266nm 0°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#63-110** CLEARANCE 3-4 DAYS

⊖ 1 ⊕ **€47,95**

ADD TO CART

Qty 1+

€47,95

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%):
>90

Back Surface:

Ground
Reflection at DWL (%): 99.5
Coating Specification: R _{abs} >99.5% @ 266nm R _{avg} >98% @ 255 - 275nm
Wavelength Range (nm): 255 - 275
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (255-275nm)
Design Wavelength DWL (nm): 266
Diameter (mm): 12.50 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 0
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, By Design: ☐ 2 J/cm² @ 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View