


TECHSPEC® 12.5mm Dia., 3mm Thick, Fused Silica 755/632nm Alexandrite Mirror, 45 Deg AOI



Stock #25-535 **20+ In Stock**

⊖ 1 ⊕ €160.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	€160,00 each
Qty 6-25	€128,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Alexandrite Laser Mirror

Type:

Physical & Mechanical Properties

3.00 ±0.10

Thickness (mm):

12.50 +0.00/-0.10

Diameter (mm):

90 **Clear Aperture (%):**

<3 **Parallelism (arcmin):**

Fine Ground **Edges:**

Optical Properties

Fused Silica (Corning 7980) **Substrate:** □

10-5 **Surface Quality:**

45 **Angle of Incidence (°):**

Laser Mirror (755nm) **Coating:**

625 - 650, 755 **Wavelength Range (nm):**

λ 10 **Surface Flatness (P-V):**

Coating Specification:
 $R_{avg} > 90\%$ @ 625 - 650nm @ 45° AOI
At 755nm $R_{sabs} \geq 99.5\%$ and $R_{pabs} \geq 99.5\%$, where
 $|R_s - R_p| \leq 0.5\%$ @ 45° AOI

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- >99.5% Reflectivity at 755nm and >90% Reflectivity at 625 – 650nm
- 10-5 Surface Quality and λ 10 Surface Flatness
- Ideal for use in Dermatological Applications

TECHSPEC® 755nm Alexandrite Laser Mirrors provide >99.5% reflectivity at 755nm for use with Alexandrite lasers at 0° or 45° angle of incidence (AOI). These mirrors also provide >90% reflectivity from 625-650nm to accommodate applications that utilize alignment beams. These mirrors feature fused silica substrates with λ 10 surface flatness and 10-5 surface quality to minimize scattering effects. TECHSPEC® 755nm Alexandrite Laser Mirrors are ideal for a range of dermatological applications such as hair removal, tattoo removal, and vascular lesion treatment. The high reflectivity combined with a slim profile makes these mirrors excellent for medical articulating arms that require multiple direction changes via reflection.