


[See all 6 Products in Family](#)

12.5mm Dia., Protective Overcoat Wire Grid Polarizer



Stock #12-648 **8 In Stock**

⊖ 1 ⊕ €374.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€374,00 each
Qty 11+	€319,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer

Type:

Note:
When the Reference Mark is orientated to the 3 or 9 o'clock position, the transmission axis runs left to right.

Physical & Mechanical Properties

10.5 Clear Aperture CA (mm):

12.50	Diameter (mm):
0.70 ±0.07	Thickness (mm):
±0.2	Dimensional Tolerance (mm):
Wire Grid	Construction:
±1.0	Alignment Tolerance (°):

Optical Properties

0 ±20	Angle of Incidence (°):
BBAR (400-700nm)	Coating:
348:1 @ 450nm 885:1 @ 550nm 1229:1 @ 650nm	Extinction Ratio:
Corning Eagle XG	Substrate: <input type="checkbox"/>
80-50	Surface Quality:
87	Transmission (%):
±2.5 @ 420 - 700nm	Transmission Tolerance (%):
R _{avg} <1% @ 400 - 700nm (Back of Substrate)	Coating Specification:
420 - 700	Wavelength Range (nm):

Material Properties

31.7 x 10 ⁻⁷ /°C	Thermal Expansion:
-----------------------------	---------------------------

Environmental & Durability Factors

-40 to +200	Operating Temperature (°C):
-------------	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Reflect S-Polarized Light, Transmit P-Polarized Light
- Protective Overcoat for Easy Handling and Cleaning
- Lighter, Thinner Design than Traditional [Wire Grid Polarizers](#)
- Overcoat Temperature Stability up to 200°C

Protective Overcoat Wire Grid Polarizers are used to reflect s-polarized light while transmitting p-polarized light in the visible spectrum. These polarizers consist of a thin aluminum wire grid attached to a glass substrate that is treated with a hard, protective coating. The overcoat protects the wire grid structure from scratches or other damage due to mechanical stress while enabling lighter, thinner designs compared to traditional [Wire Grid Polarizers](#) that use cover glass. The protective coating on these polarizers allows for them to be easily handled and cleaned, unlike [bare wire grid polarizers](#) where handling and cleaning is not recommended. Protective Overcoat Wire Grid Polarizers can be used in environments with high temperatures up to 200°C for over 1000 hours with minimal impact on performance.

Note: Reference marks indicate the axis of polarization.