

TECHSPEC® 12.5mm Dia x -15mm FL VIS 0° Coated, Negative Achromatic Lens



Stock **#62-484** 3-4 DAYS
[Other Coating Options](#)

- 1 + **€88,00**

ADD TO CART

Qty 1-5
€88,00
Qty 6+
€74,80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

-15.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): -18.08
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 6.00 ±0.10
Center Thickness CT 1 (mm): 2.00 ±0.05
Center Thickness CT 2 (mm): 4.00 ±0.05
Radius R ₁ (mm): -10.62
Radius R ₂ (mm): 8.63
Radius R ₃ (mm): 81.12
Edge Thickness ET (mm): 8.04
Substrate: N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.2
Numerical Aperture NA: 0.42
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View