

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia X -7.5mm FL VIS 0th Coated, Negative Achromatic Lens



Stock #62-489 ☒ In Stock
[Other Coating Options](#)

-

1

+

 €88,00

ADD TO CART

Qty 1-5
€88,00
Qty 6+
€74,80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

-75.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : -77.47
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.50 ±0.10
Center Thickness CT 1 (mm) : 2.50 ±0.05
Center Thickness CT 2 (mm) : 3.00 ±0.05
Radius R₁ (mm) : -46.07
Radius R₂ (mm) : 36.65
Radius R₃ (mm) : 108.00
Edge Thickness ET (mm) : 6.05
Substrate:  N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 6.00
Numerical Aperture NA : 0.08
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Negative Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View