

**TECHSPEC® 12.5mm Dia. x 17.5mm FL, VIS-NIR, Inked, Achromatic Lens**



Stock **#49-952-INK** [CONTACT US](#)  
[Other Coating Options](#)

- 1 + **€96,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €96,00                        |
| Qty 6+                        |
| €76,75                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50 ±0.025

Effective Focal Length EFL (mm):

|                                                                                                                                                    |
|----------------------------------------------------------------------------------------------------------------------------------------------------|
| 17.50                                                                                                                                              |
| Focal Length Tolerance (%):<br>±1                                                                                                                  |
| Back Focal Length BFL (mm):<br>13.59                                                                                                               |
| Focal Length Specification Wavelength (nm):<br>587.6                                                                                               |
| Clear Aperture CA (mm):<br>11.50                                                                                                                   |
| Centering (arcmin):<br><1                                                                                                                          |
| Center Thickness CT (mm):<br>7.30 ±0.10                                                                                                            |
| Center Thickness CT 1 (mm):<br>5.80 ±0.05                                                                                                          |
| Center Thickness CT 2 (mm):<br>1.50 ±0.05                                                                                                          |
| Radius R <sub>1</sub> (mm):<br>12.20                                                                                                               |
| Radius R <sub>2</sub> (mm):<br>-9.82                                                                                                               |
| Radius R <sub>3</sub> (mm):<br>-39.19                                                                                                              |
| Edge Thickness ET (mm):<br>5.08                                                                                                                    |
| Substrate: <br><a href="#">N-BAF10</a> / <a href="#">N-SF57</a> |
| Surface Quality:<br>40-20                                                                                                                          |
| f/#:<br>1.4                                                                                                                                        |
| Numerical Aperture NA:<br>0.36                                                                                                                     |
| Coating:<br>VIS-NIR (400-1000nm)                                                                                                                   |
| Coating Specification:<br>R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @400 - 870nm<br>R <sub>avg</sub> ≤1.25% @890 - 1000nm         |
| Power (P-V) @ 632.8nm:<br>1.5λ                                                                                                                     |
| Irregularity (P-V) @ 632.8nm:<br>λ/4                                                                                                               |
| Bevel:<br>Protective bevel as needed                                                                                                               |
| Type:<br>Achromatic Lens                                                                                                                           |
| Wavelength Range (nm):<br>400 - 1000                                                                                                               |

## Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| REACH 201:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |