

12.5mm Diameter, Indoor, Hydrophobic Window

See More by [SCHOTT Optical Components](#)



Stock #36-070 **14 In Stock**

⊖ 1 ⊕ €89.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€89,00 each
Qty 6-25	€80,00 each
Qty 26-99	€76,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window **Type:**

Glass **Type of Window:**

Indoor **Note:**

Physical & Mechanical Properties

11.25 Clear Aperture CA (mm):

12.50 +0.00/-0.25 Diameter (mm):

1.10 ±0.1 Thickness (mm):

Protective as needed Bevel:

90.00 Clear Aperture (%):

Fine Ground Edges:

0.20 Poisson's Ratio:

64 Young's Modulus (GPa):

480.00 Knoop Hardness (kg/mm²):

Optical Properties

Hydrophobic (425-675nm) Coating:

BOROFLOAT® Substrate:

1.472 Index of Refraction (n_d):

80-50 Surface Quality:

65.41 Abbe Number (v_d):

R_{avg} <0.5% @ 425 - 675nm Coating Specification:

425 - 675 Wavelength Range (nm):

Material Properties

2.23 Density (g/cm³):

3.25 Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Water: 90 - 105
Oil: 30 - 40 Contact Angle (°):

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



Product Details

- Oil and Water Repellent Coating
- Ideal for Industrial and Harsh Environments
- AR Coated for <0.5% Reflection in the Visible Spectrum

Hydrophobic Windows are designed to repel oil (oleophobic) and other liquids (hydrophobic), facilitating cleaning and ensuring maximum transmission of incident light. Hydrophobic treated surfaces cause liquids to form droplets on contact rather than be absorbed or spread across the surface of the optic. Hydrophobic Windows feature anti-reflection coatings to provide less than 0.5% reflection per surface from 425 – 675nm. These windows are ideal for harsh environments, portable handheld devices, or biometric measurement devices.

Indoor Hydrophobic Windows are ideal for applications where cleaning or abrasion is expected while Outdoor Hydrophobic Windows provide better performance both at elevated temperatures and under direct UV light exposure.

Technical Information



Compatible Mounts

;