

TECHSPEC®

12.5mm Dia x 75.0mm FL 532nm V-Coat, Cylinder Lens



Laser Line PCX Cylinder Lens

Stock **#33-225** CLEARANCE ☐ In Stock

⊖

1

⊕

€39,95

ADD TO CART

Qty 1+

€39,95

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[N-BK7](#)

f/#:
6.00

Numerical Aperture NA:

0.08
Coating: Laser V-Coat (532nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 495 - 570
Back Focal Length BFL (mm): 73.68
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{abs} <0.25% @ 532nm R _{avg} <1.5% @ 495 - 570nm
Design Wavelength DWL (nm): 532
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.49
Focal Length Tolerance (%): ±3
Note: Coating: 532nm V-Coat
Radius R₁ (mm): 38.76
Surface Quality: 60-40
Wavelength Range (µm): 0.495 - 0.570

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View