

TECHSPEC®

12.5mm Dia x -25mm FL VIS 0°, Inked, Negative Achromatic Lens



Stock **#62-486-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

€103⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€103,00 each
Qty 6-25	€87,55 each
Qty 26-49	€82,40 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General


Negative Achromatic Lens		Type:
Physical & Mechanical Properties		
Diameter (mm):		12.50 ±0.025
Clear Aperture CA (mm):		11.50
Centering (arcmin):		<1
Center Thickness CT (mm):		4.55 ±0.10
Center Thickness CT 1 (mm):		2.00 ±0.05
Center Thickness CT 2 (mm):		2.55 ±0.05
Edge Thickness ET (mm):		5.74
Bevel:		Protective as needed
Optical Properties		
Effective Focal Length EFL (mm):		-25.00
Focal Length Tolerance (%):		±1
Back Focal Length BFL (mm):		-27.33
Focal Length Specification Wavelength (nm):		587.6
Radius R ₁ (mm):		-17.75
Radius R ₂ (mm):		12.17
Radius R ₃ (mm):		109.75
Substrate: 		N-BAF10 / N-SF10
Surface Quality:		40-20
f/#:		2.00
Numerical Aperture NA:		0.25
Coating:		VIS 0° (425-675nm)
Coating Specification:		R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm:		1.5λ
Irregularity (P-V) @ 632.8nm:		λ/4
Wavelength Range (nm):		425 - 675
Regulatory Compliance		
Certificate of Conformance:		View

PRODUCT DETAILS

- VIS 0° and VIS-NIR Coatings
- 6.25 – 25mm Diameter Options
- [MgF₂ Coated Negative Achromatic Lenses](#) also Available

TECHSPEC® Broadband AR Coated Negative Achromatic Lenses are corrected for color and on-axis aberrations. These lenses, consisting of two optical elements cemented together, are commonly used as Barlow lenses to extend focal lengths. The achromatic lenses are available in various diameter sizes and VIS 0° or VIS-NIR coating options. TECHSPEC® Broadband AR Coated Negative Achromatic Lenses are offered in 6.25 - 25mm diameter options. [MgF₂ Coated Negative Achromatic Lenses](#) are also available.

TECHNICAL INFORMATION



COATING CURVES

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS