

[See all 6 Products in Family](#)

125mm Sq. Metric Kinematic Magnetic Base



#22-402: 125mm Sq. Metric Kinematic Magnetic Base

Stock **#22-402** **3 In Stock**

⊖ 1 ⊕ €373⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€373,00 each
Qty 10+	€336,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Metric **Type:**

Note:
The permanent magnet is turned on and off by integrated screw (5mm Hex)

Yes **Switchable:**

Physical & Mechanical Properties

125.00 **Length (mm):**

125.00 **Width (mm):**

25.40 **Thickness (mm):**

Anodized Aluminum **Construction:**

0.97 **Weight (kg):**

<70.0 **Repeatability (μ rad):**

Threading & Mounting

(71) M6 x 1.0 **Mounting Threads:**

Material Properties

40 **Magnetic Force (N):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.