


12.5mm Diameter, 1.1mm Thick, <100 Ω/sq, ITO Coated Glass Window



Indium Tin Oxide (ITO) Coated Conductive Windows

Stock **#74-469** NEW **20+ In Stock**

-

1

+

€49⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€49,00 each
Qty 11-25	€39,20 each
Qty 26-49	€36,75 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Protective Window	Type:
Physical & Mechanical Properties	
12.50 ±0.2	Diameter (mm):
	Thickness (mm):

1.10 ±0.25	
Protective as needed	Bevel:
ITO Window	Construction:
Cut and Safety Seam	Edges:
Optical Properties	
S1: ITO Coating S2: Uncoated	Coating:
Float Glass	Substrate: □
T _{avg} ≥88% from 400-700nm	Visible Light Transmission VLT (%):
<100 Ω/sq	Coating Specification:
400 - 700	Wavelength Range (nm):
Material Properties	
<100	Surface Resistivity (Ω/ Sq):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Electro Magnetic Interference (EMI) Shielding, Defogging, and Display Protection Applications
- 10Ω/sq and 100Ω/sq Coating Options
- 12.5, 25, 50, and 75 mm Sizes Available
- Conductive Tape Available for Prototyping

Indium Tin Oxide (ITO) Coated Conductive Windows feature an electrically conductive coating on float glass substrates and are available in sheet resistivities of 10 Ω/sq and 100 Ω/sq. A low sheet resistivity of 10 Ω/sq is ideal for applications requiring high conductivity, while the 100 Ω/sq resistivity is commonly used for improved heat dissipation and NIR transmission. Available in both round and square sizes from 12.5 to 75 mm, the windows feature up to 88% visible light transmission in the 400-700nm range. Indium Tin Oxide (ITO) Coated Conductive Windows are ideal for a wide variety of applications including display protection, EMI shielding, outdoor surveillance, de-fogging, and de-icing applications. Additionally, conductive tape is available to simplify prototyping and integration.