

12.5mm Diameter, Cyan Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#52-536** 20+ In Stock

-

1

+

€25⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-24	€25,00 each
Qty 25-49	€22,75 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Dichroic Filter	Type:
Physical & Mechanical Properties	
12.50	Diameter (mm):
2.00 Nominal	Thickness (mm):

Dimensional Tolerance (mm):	
±0.25	
Clear Aperture (%):	
≥85	
Optical Properties	
Angle of Incidence (°):	
0	
Cut-Off Wavelength (nm):	
590.00	
Substrate: ☐	
BOROFLOAT®	
Coating:	
Subtractive Color	
Color:	
Cyan	
Surface Quality:	
80-50	
Coating Specification:	
T _{avg} >80% @ 400 - 550nm	
T _{avg} <1.0% @ 640 - 740nm	
Cut-Off Wavelength Tolerance (µm):	
0.015	
Environmental & Durability Factors	
Operating Temperature (°C):	
<100	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 247:	
Compliant	


Product Details

- High Saturation Dichroic Type
- Matrix of Sizes and Sets
- Precision Glass Substrate

Additive and Subtractive Dichroic Color Filters are dichroic filters ideal for machine vision and commonly used for color separation and contrast enhancement applications. Provided in unmounted versions, these filters are easily integrated into a variety of existing camera and illumination setups. In addition, dichroic filters provide wider fields of view not obtainable using narrow bandpass interference filters. Additive and Subtractive Dichroic Color Filters feature a precision glass substrate and are offered in a variety of sizes and sets. A complete set of these dichroic filters is available in a [Pre-Loaded filter wheel](#).

Typical applications include photo enlargers, beam separation, and placing filters in front of an imaging lens to selectively isolate spectral regions/colors.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
