


[See all 2 Products in Family](#)

TECHSPEC® 12.7 x 50.8mm EFL 90° VIS Coated Glass Off-Axis Parabolic Mirror



High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors



Stock #18-670 **14 In Stock**

⊖ 1 ⊕ €855.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€855,00 each
Qty 6-25	€771,00 each
Qty 26-50	€728,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

50.80	Y Offset (mm):
12.70 +0/-0.10	Diameter (mm):
90	Clear Aperture (%):
<10 RMS	Surface Roughness (Å):

Optical Properties

VS	Coating:
90	Off-Set Angle (°):
400 - 750	Wavelength Range (nm):
50.80	Effective Focal Length EFL (mm):

UV Fused Silica	Substrate: <input type="checkbox"/>
Coating Specification: R _{avg} >98% @400-750nm (0°-45° AOI for All Polarizations) R _{avg} >99% @400-750nm (0°-45° AOI for S-Polarization)	

±1	Focal Length Tolerance (%):
25.4	Parent Focal Length PFL (mm):

λ/8 @ 632.8nm	Surface Figure, RMS:
40-20	Surface Quality:

0.5J/cm ² , 20ns, 20Hz @ 532nm	Damage Threshold, By Design: <input type="checkbox"/>
λ/4 @ 632.8nm	Reflected Wavefront, RMS:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- High Quality Fused Silica Substrate
 - <10Å Surface Roughness for Low Scatter
 - 90° Offset Angle for Easy Integration
- TECHSPEC® High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors feature a surface roughness of less than 10Å which is the lowest scatter available in an off-the-shelf solution. Featuring a fused silica substrate, these low scatter alternatives perform better in the UV wavelength range than traditional metallic substrate OAPs. TECHSPEC® High Performance Fused Silica Off-Axis Parabolic (OAP) Mirrors are ideal for Schlieren, MTF, and Czerny-Turner and Litrow spectrometer systems due to their low scattering.

Note: Uncoated options require a coating for use. Contact us for a custom coating quote for your specific wavelength.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).