

12.7mm Dia. 488nm λ /4 Quartz Waveplate Multiple Order



Stock **#85-074** [CONTACT US](#)

- 1 + **€257,00**

ADD TO CART

Qty 1-5
€257,00
Qty 6+
€208,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
8.00

Coating:
Laser V-Coat (488nm)

Design Wavelength DWL (nm):
488

Diameter (mm):

12.70 +0.00/-0.25
Substrate: Crystal Quartz
Retardance: $\lambda/4$
Surface Quality: 10-5
Thickness (mm): 6.40 +0.00/-0.25
Type: Crystalline Waveplate
Construction: Crystalline
Transmitted Wavefront, P-V: $\lambda/10$ for central 80% of clear aperture
Parallelism (arcsec): <3
Retardance Tolerance: $\pm\lambda/200$
Temperature Coefficient ($\lambda/^\circ\text{C}$): 0.0015
Retardance Order: Multiple Order

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View