

TECHSPEC[®] 12.7 x 12.7mm 532nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors

Stock **#39-647** 7 In Stock

-

1

+

€156⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€156,00 each
Qty 6-25	€137,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror

Type:

Physical & Mechanical Properties

<3

Parallelism (arcmin):

85

Clear Aperture (%):

Commercial Polish	Back Surface:
12.7 x 12.7 +0.00/-0.10	Dimensions (mm):
6.35 ±0.20	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.8	Reflection at DWL (%):
R _{abs} >99.8% @ 532nm	Coating Specification:
λ/10	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (532nm)	Coating:
532	Design Wavelength DWL (nm):
0-45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: □
10 J/cm ² @ 532nm, 20ns, 20Hz	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

• Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies

• High Laser Induced Damage Threshold Specifications

• 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications

• [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.

Note: Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts