


**TECHSPEC® 12.7 x 12.7mm x 50mm FL, VIS 0° Imaging Grade PCX Cylinder Lens**



Stock #34-986 [CONTACT US](#)

⊖ 1 ⊕ €100.<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €100,00 each                  |
| Qty 6-25       | €90,00 each                   |
| Qty 26-49      | €85,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cylinder Lens, Plano-Convex **Type:**

**Physical & Mechanical Properties**

**Bevel:**

Protective as needed

Center Thickness CT (mm):  
2.00

Center Thickness Tolerance (mm):  
±0.1

Clear Aperture CA (mm):  
11.43 x 11.43

Dimensional Tolerance (mm):  
+0.0/-0.025

Dimensions (mm):  
12.7 x 12.7

Edge Thickness ET (mm):  
1.21

Axial Twist (arcmin):  
<3

## Optical Properties

Effective Focal Length EFL (mm):  
50.00

Substrate:   
N-BK7

f#:  
8.00

Numerical Aperture NA:  
0.13

Coating:  
MS 0° (425-675nm)

Wavelength Range (nm):  
425 - 675

Back Focal Length BFL (mm):  
48.68

Coating Specification:  
R<sub>avg</sub> ≤ 0.4% @ 425 - 675nm

Radius R<sub>1</sub> (mm):  
25.84

Surface Quality:  
40-20

Power (P-V) @ 632.8nm:  
1.5λ

Irregularity (P-V) @ 632.8nm:  
λ/4

Plano Axis Wedge (arcmin):  
<5

Power Axis Wedge (arcmin):  
<5

## Regulatory Compliance

RoHS 2015:  
Compliant

Certificate of Conformance:  
[View](#)

Reach 235:  
Compliant

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Ideal for Beam Shaping Applications
- Tightly Controlled Optical and Geometric Tolerances
- Rectangular and Circular Form Factors Available

TECHSPEC® Imaging Grade PCX Cylinder Lenses offer an ideal pairing of tightly controlled tolerances and scalable pricing for volume integration. As opposed to spherical lenses, which focus light in two dimensions, cylinder lenses are used to focus light in one dimension. AR Coating options are available for laser applications, minimizing stray light and maximizing throughput of a system. Our TECHSPEC Imaging Grade PCX Cylinder Lenses are specified to control geometric characteristics in order to ensure consistent performance from design to manufacturing. Typical applications include circularizing elliptical beams from a laser diode, creating a light sheet for

measurement systems, or projecting a laser line onto a surface.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC Imaging Grade PCV Cylinder Lenses](#).



## Coating Curves

---