


[See all 18 Products in Family](#)

12.7mm Dia., 5 Arcsec, Bare Gold Replicated Hollow Metal Retroreflector



Replicated Hollow Metal Retroreflectors

Stock **#15-897** **6 In Stock**

-

1

+

€495⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€495,00 each
Qty 10-24	€460,35 each
Qty 25+	€420,75 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Retroreflector

Style:

Standard Profile

Physical & Mechanical Properties

Clear Aperture CA (mm):


10.16	
	Diameter (mm):
12.70	
	Height (mm):
21.68	
	Dimensional Tolerance (mm):
+0.025/-0.051	
Optical Properties	
	Beam Deviation (arcsec):
5	
	Coating:
Bare Gold	
	Substrate: ☐
Aluminum	
	Surface Quality:
60-40	
	Image Orientation:
Left-Handed	
	Coating Specification:
R _{avg} >94% @ 700 - 800nm	
R _{avg} >97% @ 800 - 2000nm	
R _{avg} >98% @ 2 - 12μm	
	Ray Deviation (°):
180	
	Wavelength Range (nm):
700 - 12000	
Threading & Mounting	
	Mounting Threads:
10-24	
Regulatory Compliance	
	Certificate of Conformance:
View	

Product Details

- Monolithic Aluminum Construction
- Return Beam Accuracy Unaffected by Vibration
- Bare Gold or Enhanced Aluminum Coating Options
- Low Profile Versions are Available

Replicated Hollow Metal Retroreflectors feature a monolithic aluminum construction and an integrated mount to provide return beam performance unaffected by vibration. These retroreflectors are offered with bare gold coatings applied to the first surface, maximizing their reflectivity in the infrared (IR), or enhanced aluminum coatings for optimal performance in the visible spectrum. Designed to have the entirety of their optical path in air, these retroreflectors do not require antireflection coatings for optimal performance and can be used over wider wavelength ranges than glass retroreflectors. Replicated Hollow Metal Retroreflectors are ideal for applications where an optical path through a glass prism is undesired, reduced weight is required, or where high shock and vibration levels are expected. The replication manufacturing process of these optics enables cost-effective designs while providing high performance beam return accuracy.

Technical Information



REPLICATED HOLLOW METAL RETROREFLECTORS					
Diameter (mm)	Height (mm)	Mounting Threads	Coating	Stock No.	
				5 Arcseconds	10 Arcseconds
12.7	21.68	10-24	Bare Gold	#15-897	#15-898
19.1	26.17	10-24	Bare Gold	#15-899	#15-900
25.4	30.66	10-24	Bare Gold	#15-901	#15-902
38.1	39.64	10-24	Bare Gold	#15-903	#15-904

LOW PROFILE REPLICATED HOLLOW METAL RETROREFLECTORS						
Dimension A (mm)	Dimension B (mm)	Dimension C (mm)	Coating	Stock No.		
				2 Arcseconds	5 Arcseconds	10 Arcseconds
12.7	8.63	12.8	Bare Gold	N/A	#23-854	#23-855
25.4	21.69	20.32	Bare Gold	#23-856	#23-857	#23-858