

[See all 293 Products in Family](#)

TECHSPEC® 12.7mm Dia. x 38.1mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#49-775-INK** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ €102.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€102,00 each
Qty 6-25	€81,00 each
Qty 26-49	€77,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

12.70 ±0.025	Diameter (mm):
11.70	Clear Aperture CA (mm):
<1	Centering (arcmin):
5.00 ±0.20	Center Thickness CT (mm):
3.50 ±0.10	Center Thickness CT 1 (mm):
1.50 ±0.10	Center Thickness CT 2 (mm):
3.92	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties

38.10	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
35.57	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
25.43	Radius R₁ (mm):
-20.03	Radius R₂ (mm):
-74.39	Radius R₃ (mm):
N-SSK8 / SF56	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
3.00	f#:
0.17	Numerical Aperture NA:
VIS 0° (425-675nm)	Coating:
R _{avg} ≤0.4% @ 425 - 675nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
425 - 675	Wavelength Range (nm):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- [MgF₂](#) and [VIS-NIR](#) Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. Achromatic lenses are best for applications involving multi-color (white light) imaging due to their specific doublet lens pairing that enables them to correct the color separation inherent in glass. TECHSPEC® VIS 0° Coated

Technical Information



Coating Curves

Compatible Mounts