

TECHSPEC® 12mm Diameter x 36mm FL, 532nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#67-961** 3-4 DAYS

[Other Coating Options](#)



1



€183,00

ADD TO CART

Qty 1-5

€183,00

Qty 6+

€146,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.00/-0.10

Effective Focal Length EFL (mm):
36.00 @ 587.6nm

Back Focal Length BFL (mm):

34.29
Coating: Laser V-Coat (532nm)
Coating Specification: R _{abs} <0.25% @ 532nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.05
Edge Thickness ET (mm): 1.37
Radius R₁ (mm): 16.51
Clear Aperture CA (mm): 10.2
f/#: 3.00
Numerical Aperture NA: 0.17
Design Wavelength DWL (nm): 532
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 10 J/cm ² @ 10ns

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View