

**TECHSPEC® 12mm Dia. x 50mm FL VIS 0° Coated, UV Plano-Convex Lens**



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#48-959** 3-4 DAYS

- 1 + **€130,00**

ADD TO CART

Qty 1-5

€130,00

Qty 6+

€104,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
12.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**

|                                                                           |
|---------------------------------------------------------------------------|
| 50.00 @ 587.6nm                                                           |
| <b>Back Focal Length BFL (mm):</b><br>48.01                               |
| <b>Coating:</b><br>VS 0° (425-675nm)                                      |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm     |
| <b>Substrate:</b> <a href="#">Fused Silica</a> (Coming 7980)              |
| <b>Surface Quality:</b><br>40-20                                          |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                     |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                               |
| <b>Focal Length Tolerance (%):</b><br>±1                                  |
| <b>Centering (arcmin):</b><br><1                                          |
| <b>Center Thickness CT (mm):</b><br>2.90 ±0.05                            |
| <b>Edge Thickness ET (mm):</b><br>2.10                                    |
| <b>Radius R<sub>1</sub> (mm):</b><br>22.92                                |
| <b>Clear Aperture CA (mm):</b><br>11                                      |
| <b>f/#:</b><br>4.17                                                       |
| <b>Numerical Aperture NA:</b><br>0.12                                     |
| <b>Type:</b><br>Plano-Convex Lens                                         |
| <b>Bevel:</b><br>Protective bevel as needed                               |
| <b>Wavelength Range (nm):</b><br>425 - 675                                |
| <b>Damage Threshold, Reference:</b> <a href="#">5 J/cm² @ 532nm, 10ns</a> |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |