

TECHSPEC[®] 135mm EFL MgF₂ Coated, UV-NIR Corrected Triplet



Stock **#64-839** 1 In Stock

-

1

+

€2.860⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€2.860,00 each
Qty 6-10	€2.430,00 each
Qty 11-25	€2.290,00 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Triplet Lens

Type:

Physical & Mechanical Properties

22.5

Clear Aperture CA (mm):

30.00 ±0.05

Housing Diameter (mm):

20.50 ±0.05	Housing Length (mm):
Optical Properties	
135.00	Effective Focal Length EFL (mm):
±1.5 @ 248nm	Focal Length Tolerance (%):
129.31	Back Focal Length BFL (mm):
126.9	Back Focal Length BFL from Housing (mm):
CaF ₂ / Fused Silica / CaF ₂	Substrate: ☐
60-40	Surface Quality:
6.00	f#:
0.08	Numerical Aperture NA:
MgF ₂ (193-1000nm)	Coating:
MgF ₂ @600nm	Coating Specification:
135.00	Effective Focal Length EFL @ 248nm (mm):
193 - 1000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 205:
View	Certificate of Conformance:

Product Details

• Calcium Fluoride and UVFused Silica Elements


• Broadband Color-Corrected Design from 193nm to 1000nm

• Ideal for Fluorescence and Spectroscopy Applications

TECHSPEC® UV-to-NIR Corrected Triplet Lenses provide a consistent focal length (see chromatic shift information below) for wavelengths ranging from 193nm to 1000nm. These lenses were designed with broadband applications in mind. Manufactured with premier grades of Calcium Fluoride and Fused Silica, these infinite-conjugate triplets are perfect for imaging applications utilizing a wide spectrum of wavelengths. TECHSPEC® UV-to-NIR Corrected Triplet Lenses are typically used for fluorescence research in which the emitted light is in the visible and near infrared regions of the spectrum or in dual-pass systems in which the same lens is used to illuminate the excitation material as well as collect the emissions from it. Elements are uncoated and mounted in a 30mm diameter aluminum housing. Antireflection coatings available, however a minimum order quantity will apply.

Full [prescription](#) information available.

Technical Information



Effective Focal Length EFL	193 - 400nm		400 - 1000nm		193 - 1000nm	
	Chromatic Shift	RMS Spot Size	Chromatic Shift	RMS Spot Size	Chromatic Shift	RMS Spot Size
36mm	1.8mm	240µm	0.4mm	214µm	2.2mm	268µm
45mm	1.1mm	88µm	0.3mm	69µm	1.3mm	95µm

90mm	2.0mm	64μm	0.6mm	38μm	2.5mm	69μm
135mm	1.6mm	49μm	0.6mm	31μm	2.1mm	51μm
180mm	1.4mm	46μm	0.6mm	28μm	1.9mm	45μm
