

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #20-240 3-4 DAYS



1



€39,00

ADD TO CART

Qty 1-10

€39,00

Qty 11+

€33,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Extinction Ratio:
Up to 7,500:1

Substrate:
[Polymer Film XP38](#)

Operating Temperature (°C): -20 to +70
Dimensions (inches): 5.91 x 5.91
Dimensions (mm): 150.0 x 150.0
Thickness (inches): 0.007 ±0.001
Thickness (mm): 0.19 ±0.02
Transmission (%): Single: 38.5 ±2 Parallel: 30.1 Crossed: <0.004
Type: Linear Polarizer
Dimensional Tolerance (mm): +1.0/-1.0
Construction: Polarizing Film
Note: Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98
Heat Resistance (°C x Hours): 70 x 240
Humidity Resistance (°C x Hours): 40 x 95% RH x 240
Transmission Variance after 1000 Hours (%): <±5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant