

TECHSPEC® 1550nm, 25.4mm Dia. x 6.35mm Thickness, Ultrafast Laser Mirror



Stock **#26-842** NEW 3-4 DAYS

- 1 + **€154,00**

ADD TO CART

Qty 1-5
€154,00

Qty 6+
€145,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45

Coating:
Ultrafast (1510-1590nm)

Design Wavelength DWL (nm):
1550

Diameter (mm): 25.40 +0.00/-0.10
Substrate: Fused Silica (Coming 7980)
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Mirror
Parallelism (arcmin): <3
Clear Aperture (%): 90
Durability: ML-PRF-13830B
Back Surface: Commercial Polish
Coating Specification: R _(avg) S & P >99.90% @ 1550nm @ 45° AOI R _(avg) >99.7% @ 1510 - 1590nm @ 45° AOI
Wavelength Range (nm): 1510 - 1590
Surface Flatness (P-V): λ/8
Coating Type: Dielectric
GDD Specification: ±20 fs ² @ 1510 - 1590nm @ 45° AOI (s-pol) ±30 fs ² @ 1530 – 1580nm @ 45° AOI (p-pol)

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View