

TECHSPEC® 15mm Dia., 0.67 NA, V-Coated 1550nm NIR Aspheric Lens



Stock #22-935 3-4 DAYS

- 1 + **€340,00**

ADD TO CART

Qty 1-5
€340,00

Qty 6+
€272,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
11.25 @ 1550nm

Numerical Aperture NA:
0.67

Back Focal Length BFL (mm): 7.88 @ 587.6nm
Substrate: ☐ N-SF6
Aspheric Design Wavelength (nm): 1550
Coating: 1550nm V-Coat
Coating Specification: R _{abs} < 0.25% @ 1550nm @ 0° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 1.5
Center Thickness CT (mm): 5.00 ±0.1
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Durability: ADHESION AND ABRASION AS PER MIL-PRF13830B APP C, PARA C.3.8.4 AND C.3.8.5
Damage Threshold, By Design: ☐ 5 J/cm² @ 1550nm, 10ns
Asphere Figure Error, @ 632.8nm: 0.4λ RMS and 2λ PV
Power (diopters): 88.89

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant