

[All Products](#) / [Laser Optics](#) / [Laser Optics](#) / [Jenoptik JENar™ Silverline™ F-Theta](#)

[See all 12 Products in Family](#)

160mm, 900-1100nm F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock #17-021 [CONTACT US](#)

- 1 +

€6.885^{,00}

ADD TO CART

Volume Pricing	
Qty	€6.885,00
1+	each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
STEP:step	PDF Drawing:pdf
IGES:igs	Spec Sheets:pdf
Zemax:zar	eDrawing:eprt
Code V:seq	EO Spec Sheet
Download All	

General

Model Number: 601787	Type: JENar Silverline F-Theta
Protective Window: #17-694: One Included	Manufacturer: Jenoptik

Physical & Mechanical Properties

Maximum Diameter (mm): 119.8 +0/-0.2	Weight (g): 1080
X/Y Mirror Angle (°): ±7.1	Flange Distance (mm): 266.00 @ 900nm 267.90 @ 1100nm
Input Beam Diameter, 1/e² (mm): 14	Maximum Length (mm): 100

Optical Properties

Focal Length FL (mm): 160.00	Substrate: Fused Silica (Corning 7980)
Scan Angle (°): ±20	Scan Field (mm): 78 x 78
Telecentricity (°): F-Theta Only: 5.20 With Scanner: 5.40	Working Distance (mm): 182.00 @ 900nm 183.90 @ 1100nm
Wavelength Range (nm): 900 - 1100	Scan Field Diameter (mm): 110
Focus Size Diameter, 1/e² (µm): 19.0 @ 900nm 23.0 @ 1100nm	GDD Specification (fs²): 759

Threading & Mounting

Mounting Threads: M85 x 1

Regulatory Compliance

Certificate of Conformance: [View](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Product Details

- Low-Absorption Fused Silica Substrates for High-Power Laser Applications
- Large Scan Fields Up to 328mm x 328mm
- High Damage Thresholds and Low Telecentricity Errors
- **Jenoptik JENar™ F-Theta Scanning Lenses** Also Available

Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses provide flat field at the image plane and feature low-absorption fused silica substrates, making them suitable for high-power laser applications. These F-Theta lenses offer high damage thresholds to handle beam powers of up to four kilowatts without active cooling and are available in various wavelengths ranging from 266nm to 1100nm. With large processing areas up to 328mm x 328mm, low telecentricity errors, and diffraction-limited image quality, these lenses allow for high spot consistency and increased throughput over the entire scanning range. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses were specially developed for applications requiring high-power and short-pulse Nd:YAG, Yb:doped, and fiber laser sources and are used in conjunction with [galvanometers](#) and [beam expanders](#).

Contact us if your application requires [Jenoptik JENar™ F-Theta Scanning Lenses](#) or Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses not shown on our website.

Accessories

Note: Compatible accessories for individual stock numbers may vary. If unsure about which accessories work with your products, please contact us [here](#).

	Title	Compare	Stock Number	Price	Buy
MORE+	Protective Window for #16-768		#17-690	€310,00 Request Quote	CONTACT US 1
MORE+	Protective Window for #16-769 and #16-770		#17-693	€545,00 Request Quote	CONTACT US 1
MORE+	Protective Window for #17-021 and #17-022		#17-694	€830,00 Request Quote	CONTACT US 1
MORE+	Protective Window for #17-026		#17-695	€870,00 Request Quote	CONTACT US 1
MORE+	Protective Window for #16-771		#17-698	€865,00 Request Quote	CONTACT US 1

Related Products



RAYLASE Galvanometer Optical Scanners



Draconis® Nd:YAG Laser Line Beam Expanders

Resources

Media Type

- Application Note
- Technical Tool
- Glossary
- Scientific Paper
- Video
- Published Article
- FAQ

APPLICATION NOTE

Chemically...

APPLICATION NOTE

Anti-Reflection...

TECHNICAL TOOL

Gaussian
Beams
Calculator

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

GLOSSARY

F-Theta
Scanning Lens

SCIENTIFIC PAPER

Development
of a Robust
Laser Damage
Threshold...

SCIENTIFIC PAPER

Development
of US national
laser damage
standard: 20...

[View More](#)