

# 1.74mm FL, IR-Cut Filter at 650nm, f/2.8, Micro Video Lens



Stock **#66-881** CLEARANCE CONTACT US

-

1

+

€32<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €32,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

## SPECIFICATIONS

### General

Series:

Long Working Distance Optimized Imaging Lenses

Note:

IR Cut-Off Filter Included

Type:

|                                  |                                               |
|----------------------------------|-----------------------------------------------|
| M12 Imaging Lens                 |                                               |
| Yes                              | IR Cut Filter:                                |
| IR-Cut Filter                    | Special Type of Lens:                         |
| Physical & Mechanical Properties |                                               |
| Fixed                            | Iris Option:                                  |
| 19.60                            | Length (mm):                                  |
| 21.0                             | Maximum Diameter (mm):                        |
| 21                               | Outer Diameter (mm):                          |
| Optical Properties               |                                               |
| 114.4                            | Horizontal Field of View @ Max Sensor Format: |
| 4.50                             | Maximum Image Circle (mm):                    |
| 124 lp/mm @ 20% Contrast         | Resolution, On-Axis:                          |
| 87 lp/mm @ 20% Contrast          | Resolution, 0.7 Field:                        |
| 30 lp/mm @ 20% Contrast          | Resolution, Full Field:                       |
| 1.74                             | Focal Length FL (mm):                         |
| 400 - ∞                          | Working Distance (mm):                        |
| f/2.8                            | Aperture (f/#):                               |
| -60 @ Full Field                 | Distortion (%):                               |
| -60                              | Maximum Distortion (%):                       |
| VS (IR-Cut Filter)               | Lens Wavelength Range:                        |
| Sensor                           |                                               |
| 1/4"                             | Maximum Sensor Format:                        |
| 3.45                             | Pixel Size (µm):                              |
| Threading & Mounting             |                                               |
| N/A                              | Filter Thread:                                |
| S-Mbunt (M12 x0.5)               | Mount:                                        |
| Regulatory Compliance            |                                               |
| Compliant                        | Reach 205:                                    |
| View                             | Certificate of Conformance:                   |



## PRODUCT DETAILS

- Up to 2/3", S-Mount Lens
- Wide Field of View Board Camera Lens
- 1.68mm to 50mm Focal Length

Long Working Distance Optimized Imaging Lenses are designed for use in micro sensor board cameras. These lenses provide excellent image quality in a small, versatile package. Optimized to cover 2/3" sensor formats, they are an ideal choice for wide angle and close focus applications. Long Working Distance Optimized Imaging Lenses have 1.68 to 50mm focal lengths. All lenses are threaded for M12 x0.5. Some models with Back Focal Distances (dimension "C") less than 4mm may be incompatible with some color cameras due to the camera's Bayer filter. We recommend such lenses for use with monochrome cameras only. Lenses are designed for the 400nm to 700nm range.

**Note:** A line of [M12 Imaging Lens Accessories](#) is available for these products.

## TECHNICAL INFORMATION



| Stock #                                                                                                                                                            |                      | Focal Length (mm) | Aperture (f/#) | A (mm) | B (mm) | C (mm) | D (mm) | E (mm) |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|-------------------|----------------|--------|--------|--------|--------|--------|
| No-IR Cut Filter                                                                                                                                                   | IR Cut Filter @650nm |                   |                |        |        |        |        |        |
| #59-776                                                                                                                                                            | #66-880              | 1.68              | 2.5            | 15.0   | 13.2   | 3.3    | 2.8    | 15.1   |
| #56-774                                                                                                                                                            | #66-881**            | 1.74              | 2.8            | 21.0   | 19.61  | 3.33   | 3.2    | N/A    |
| #64-106                                                                                                                                                            | -                    | 1.9               | 2.0            | 17.0   | 14.58  | 4.2    | 4.0    | 15.24  |
| #55-569                                                                                                                                                            | #66-883              | 2.1               | 2.0            | 17.0   | 18.3   | 4.8    | 3.7    | 19.4   |
| #57-681                                                                                                                                                            | #66-884***           | 2.5               | 2.5            | 17.0   | 19.1   | 4.4    | 3.7    | 20.3   |
| #55-570                                                                                                                                                            | #66-885              | 2.9               | 2.0            | 15.0   | 17.4   | 5.2    | 5.8    | 17.8   |
| #59-778                                                                                                                                                            | #66-886              | 3.0               | 2.0            | 14.0   | 15.3   | 5.3    | 3.9    | N/A    |
| #57-684                                                                                                                                                            | #66-890              | 6.05              | 1.8            | 15.0   | 15.6   | 8.0    | 6.0    | N/A    |
| #55-573                                                                                                                                                            | #66-891              | 6.37              | 2.4            | 14.8   | 13.12  | 5.3    | 3.3    | N/A    |
| #55-574                                                                                                                                                            | #66-892              | 8.0               | 2.5            | 15.0   | 13.5   | 5.8    | 3.0    | N/A    |
| #63-762                                                                                                                                                            | #59-779              | 10.1              | 2.8            | 15.0   | 13.4   | 6.1    | 3.2    | N/A    |
| #65-251                                                                                                                                                            | #64-107              | 10.4              | 2.8            | 14.0   | 8.93   | 6.4    | 4.0    | N/A    |
| #56-775                                                                                                                                                            | #66-893              | 12.0              | 2.0            | 14.0   | 12.1   | 6.2    | 4.0    | N/A    |
| #64-108                                                                                                                                                            | #66-894              | 16.0              | 2.0            | 14.0   | 14.4   | 8.0    | 4.5    | N/A    |
| #83-107                                                                                                                                                            | -                    | 16.0              | 4.0            | 14.0   | 14.4   | 8.0    | 4.5    | N/A    |
| #56-776                                                                                                                                                            | #66-895              | 25.0              | 2.5            | 25.0   | 23.2   | 8.1    | 6.7    | N/A    |
| #59-780                                                                                                                                                            | #66-896              | 35.0              | 2.0            | 25.0   | 23.4   | 15.8*  | 6.0    | N/A    |
| #59-781                                                                                                                                                            | #66-897              | 50.0              | 2.5            | 27.0   | 52.8   | 4.1    | 8.0    | N/A    |
| *Note: 35.0mm lens has a large flange focal length. Please make proper adjustments when mounting.<br>**#66-881, B(mm): 20.49<br>***#66-884, B(mm): 19.8, E(mm): 21 |                      |                   |                |        |        |        |        |        |

| Stock # | Focal Length (mm) | Aperture (f/#) | A (mm) | B (mm) | C (mm) | D (mm) | E (mm) |
|---------|-------------------|----------------|--------|--------|--------|--------|--------|
| #88-587 | 3.0               | 2.0            | 15.0   | 15.35  | 5.2    | 4      | 16     |
| #88-588 | 3.5               | 2.5            | 15.0   | 15.4   | 6.9    | 4      | N/A    |
| #11-323 | 3.7               | 1.6            | 19     | 24.04  | 5.46   | 6.5    | 24.16  |
| #11-324 | 4.0               | 1.8            | 20     | 23.8   | 5.01   | 7      | 24.72  |
| #88-589 | 4.0               | 2.0            | 15.0   | 16.1   | 5.9    | 3.8    | N/A    |
| #88-590 | 4.3               | 2.0            | 22.0   | 20.96  | 5.5    | 6      | 21.93  |
| #11-325 | 4.6               | 1.6            | 19     | 24.18  | 5.44   | 7      | 24.32  |
| #88-591 | 4.6               | 2.0            | 12.0   | 13.1   | 1.9    | 6      | N/A    |

|         |      |     |      |       |      |      |       |
|---------|------|-----|------|-------|------|------|-------|
| #88-592 | 5.6  | 2.0 | 17.0 | 22.21 | 5.3  | 5    | 22.38 |
| #89-750 | 6.0  | 2.0 | 14.0 | 15.1  | 6.7  | 3.93 | N/A   |
| #11-326 | 7.0  | 1.6 | 19   | 25.24 | 5.47 | 7.2  | 24.2  |
| #89-751 | 8.0  | 2.0 | 15.0 | 14.4  | 6.8  | 4.5  | N/A   |
| #89-752 | 12.0 | 2.0 | 15.0 | 14.3  | 5.7  | 4.5  | N/A   |

---