

TECHSPEC[®] 16mm, f/1.6 Cw Series Fixed Focal Length Lens



16mm Focal Length



Stock #15-638 2 In Stock

-

1

+

€316^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	€316,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Cw Series	Series:
C-Mount compatible with O-ring 25mm ID x2mm	Note:
Fixed Focal Length Lens	Type:

Meets IEC IPX7 and IPX9K		Imaging Lens Type:
Physical & Mechanical Properties		
Fixed	Iris Option:	
48.60	Length (mm):	
37.77	Maximum Diameter (mm):	
34.1	Outer Diameter (mm):	
1.9	Maximum Rear Protrusion (mm):	
38.00	Diameter (mm):	
Optical Properties		
Horizontal Field of View @ Max Sensor Format: 65.5mm - 27.8°		
Field of View at Max Sensor Format: Horizontal: 31° Vertical: 23.4° Diagonal: 38.3°		
27.8°	Horizontal Field of View, 2/3" Sensor:	
22.9°	Horizontal Field of View, 1/1.8" Sensor:	
20.4°	Horizontal Field of View, 1/2" Sensor:	
18.5°	Horizontal Field of View, 1/2.5" Sensor:	
15.3°	Horizontal Field of View, 1/3" Sensor:	
11.5°	Horizontal Field of View, 1/4" Sensor:	
11.00	Maximum Image Circle (mm):	
0.0407	Numerical Aperture NA, Object Side:	
7 (6)	Number of Elements (Groups):	
16.00	Focal Length FL (mm):	
100 - ∞	Working Distance (mm):	
f/1.6	Aperture (f/#):	
425 - 675nm BBAR	Coating:	
425 - 675nm BBAR	Coating Specification:	
12.97	Entrance Pupil Position (mm):	
25.15	Object Space Principal Plane (mm):	
-3.00	Image Space Principal Plane (mm):	
-1.26	Maximum Distortion (%):	
-53.79	Exit Pupil Position (mm):	
VIS	Lens Wavelength Range:	
Sensor		
2/3"	Maximum Sensor Format:	
2.74	Pixel Size (µm):	
Threading & Mounting		
M30.5 x0.50 (Female)	Filter Thread:	
	Mount:	

C-Mount

Environmental & Durability Factors

IPX7 and IPX9K	Environmental Rating:
-20 to +60	Storage Temperature (°C):
Waterproof (IPX7 and IPX9K)	Type of Ruggedization:

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

Product Details


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- Cw Series: Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


Technical Information




#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Distortion Plot




#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f1.6



#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f1.6



#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f1.6



#15-638, 16mm, f/1.6 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f1.6