

**TECHSPEC® 19.1mm Dia. 355nm 0-45°, Nd:YAG Laser Line Mirror**



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock #38-865 **16 In Stock**

⊖ 1 ⊕ €162.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€162,00 each
Qty 6-25	€143,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Laser Mirror **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

Commercial Polish	<b>Back Surface:</b>
19.10 +0.00/-0.10	<b>Diameter (mm):</b>
6.35 ±0.20	<b>Thickness (mm):</b>
<b>Optical Properties</b>	
10-5	<b>Surface Quality:</b>
99.8	<b>Reflection at DWL (%):</b>
$R_{\text{abs}} \geq 99.8\% @ 355\text{nm}$	<b>Coating Specification:</b>
351 - 358	<b>Wavelength Range (nm):</b>
λ/10	<b>Surface Flatness (P-V):</b>
Dielectric	<b>Coating Type:</b>
Laser Mirror (355nm)	<b>Coating:</b>
355	<b>Design Wavelength DWL (nm):</b>
0-45	<b>Angle of Incidence (°):</b>
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>
5 J/cm <sup>2</sup> @ 355nm, 20ns, 20Hz	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>

<b>Regulatory Compliance</b>	
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
  - High Laser Induced Damage Threshold Specifications
  - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
  - [TECHSPEC® Laser Mirror Substrates](#) and [TECHSPEC® Yb:YAG Laser Line Mirrors](#) Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

## Compatible Mounts

;