

TECHSPEC® 18mm Dia. x 35mm FL, YAG-BBAR Coated, Achromatic Doublet Lens



YAG-BBAR Coated Achromatic Lenses



Stock **#15-477** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€97,00**

ADD TO CART

Qty 1-5
€97,00

Qty 6+
€77,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm): 35.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 30.72
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 17.00
Centering (arcmin): <1
Center Thickness CT (mm): 7.61 ±0.20
Center Thickness CT 1 (mm): 6.01 ±0.10
Center Thickness CT 2 (mm): 1.60 ±0.10
Radius R₁ (mm): 24.26
Radius R₂ (mm): -16.23
Radius R₃ (mm): -152.99
Edge Thickness ET (mm): 5.61
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.94
Numerical Aperture NA: 0.26
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 500 - 1100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View