

2" x 2" 530nm Collimated Backlight (Recertified 05-P)

See More by [Advanced Illumination](#)



Advanced Illumination Side-Fired Collimated LED Backlight

Stock **#73-831-RCD-05P** RECERTIFIED **1 In Stock**

-

1

+

€1.000⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.000,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Model Number:

BX2-050050530ICC

LED Lifetime (hours):

50,000

LED Illuminator	Type of Illumination:
Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	Note:
Advanced Illumination	Manufacturer:
Collimated Backlight	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
106.7 L x 106.7 W x 19.1 T	Dimensions (mm):
2 x 2	Active Area (inches):
Optical Properties	
Green	Color:
530	Wavelength (nm):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Environmental & Durability Factors	
0 - 35	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Collimated Light Source for Precision Silhouetting Applications
- High Intensity and Low Heat Output
- Low Divergence Angles Compared to Non-Collimated Backlights

Advanced Illumination Edge-lit Collimated LED Backlights provide highly uniform, collimated illumination with low heat output. The low divergence angle of the light rays make them ideal for use with [telecentric imaging lenses](#). While the light rays exiting standard backlights have wide and diffuse angles, the light rays exiting these backlights are collimated at lower divergence angles for improved edge contrast in silhouetting applications such as web inspection and defect detection. While [Telecentric Illuminators](#) with highly collimated light rays are ideal high precision measurement and gauging applications, they can be large and cost restrictive. Collimated Backlights can be a great option for space-limited measurement applications.