

[See all 33 Products in Family](#)

20 x 20mm, 800µm Pitch, 1.7° Div., Double Cyl. Lens Array UV-VIS



Stock #72-606 **3 In Stock**

- 1 + €765⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-10 | €765,00 each |
| Qty 11+ | €612,00 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Lens Array **Type:**

Physical & Mechanical Properties

20.0 x 20.0 ±0.10 **Dimensions (mm):**

11.100 **Radius R (mm):**

2.00 ±0.10 **Thickness (mm):**

Optical Properties

Effective Focal Length EFL (mm):
24.70 @ 1064nm

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
UV-NIR (250-700nm)

Wavelength Range (nm):
250 - 700

Coating Specification:
R_{abs} ≤1.0% from 350 - 450nm @ 0° AOI
R_{avg} ≤1.5% @ 250 - 700nm @ 0°

Divergence Angle (°):
1.7 (Full Width)

Pitch (µm):
800.00

Array Type:
Double-Sided (with cross-oriented lenses)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 250:
[Compliant](#)

Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.